



Digital extension cable for SC sensors, 0.35 m

Kat. číslo produktu: LZX847
EUR Cena bez DPH: Kontaktujte nás
Dostupné

Technické údaje

Dĺžka kábla:	0.35 m
Kódovanie drôtu:	AWG 22: brown (+12 V DC) Black (circuit common) AWG 26: white (data -) blue (data +)
Materiál:	Cable: Cu: AWG 22 - 19×0.15 mm AWG 26 - 18×0.10 mm
Minimal bend radius:	7.5 × outer diameter, flexible installation
Minimal bend radius 2:	5 × outer diameter, fixed installation
Normálne napätie:	250 V V _{pp}
Odpor drôtu:	max. 260 Ω/km AWG 26 at 20 °C (loop)
Odpor izolácie:	≥ 20 MΩ × km at 20 °C
Odporová vlna:	ca. 95 Ω at 1 kHz, AWG 22 pairs
Odtienenie:	Cu netting, tinned
Outside coat:	PUR (Elastoplan 1185), RoHS-conformal
Prevádzková teplota:	0 - 80 °C Fixed Installation
Priemer, vonkajší:	6.8 mm ± 0.3 mm
Shield attenuation:	≥ 55 dB
Skúšobné napätie:	750 V V _{rms}

wire/shield