



A1100 O₂ sensor, ATEX, Stainless Steel, FFKM/FFPM O-rings, cap with grille; ATEX certified only when used with an ATEX 36xxEx instrument

Kat. číslo produktu: A110E-SKS

ZASTARANÁ POLOŽKA
Táto položka už nie je dostupná.

Technické údaje

Body Material:	Stainless Steel
Čas odozvy:	2935A-A: 2.5 min 2952A-A: 38 s 2956A-A: 7.2 s 29552A-A: 90 s
Certifikácia:	2004/108/EC - EN 61326-1
Hmotnosť:	0.3 kg
Materiál:	O-Rings: FFKM/FFPM
Obsah balenia:	Sensor only. Controller, sensor cable, flow-chamber or process connection must be ordered separately.
Presnosť:	±1% of reading, or ± lower measurement range, whichever is greater
Prietoková rýchlosť:	Recommended flow rate in flow chamber 2935A-A : 25 mL/min 2952A-A : 50 mL/min 2956A-A : 180 mL/min 29552A-A : 50 mL/min
Rozsah merania:	Range at 25 °C 2935A-A: 10 ppb - 400 ppm or 20 Pa - 1,000 kPa 2952A-A: 1 ppb - 80 ppm or 5 Pa - 200 kPa 2956A-A: 0.1 ppb - 20 ppm or 0.25 Pa - 50 kPa 29552A-A: 2 ppb - 80 ppm or 5 Pa - 200 kPa

Rozsah vlnových dĺžok:	Stainless Steel 1.4404 (AISI 316L), surface finish: N5, Ra < 0.4 µm
	Membrane (see specification table).
	No O-rings are in contact with the sample.
Teplota prostredia:	-5 - 100 °C (23 - 212 °F) (due to electrolyte, but sensor will not be damaged up to 200°C / 392°F) (mechanical)
Teplotný rozsah:	-5 - 60 °C (23 - 140 °F), without grille, during measurement or
	-5 - 95 °C (23 - 203 °F), with grille
Trieda ochrany:	IP68
Vzorka: tlak:	0 - 100 bar
Záruka:	24 mesiacov

Obsah balenia

Sensor only. Controller, sensor cable, flow-chamber or process connection must be ordered separately.