



Desiccator, Vacuum

Kat. číslo produktu:	2088800
EUR Cena bez DPH:	Kontaktujte nás
Dátum odoslania neuvedené	

Round polycarbonate cover and polypropylene base create implosion-proof chamber at full vacuum. Chamber is impervious to alkali and acidic conditions. Recessed rim prevents grease (not included) from contacting bench surfaces when removed and eliminates need for a separate gasket. Vacuum model features leak-proof stopcock. Dimensions (height x diam): 245 mm x 330 mm (9.7" x 13"). Holds 454 g (1 lb) of dessicant. Ceramic dessicator plate (sold separately) is inert, non-stick, and corrosion resistant. Quadrants crafted into plate for easy tracking of material locations. Plate diameter: 230 mm (9").

Technické údaje

Veľkosť balenia:	1 each
------------------	--------