



EZ1036 Sulphate Analyser

Kat. číslo produktu: **EZ1036.XXXXXXXXXX**
EUR Cena bez DPH: Kontaktujte nás

Online colorimetric analysis of Sulphate in water

EZ1000 Sulphate Analysers achieve excellent precision and accuracy. At the heart of the colorimeter there is a compact photometer assembly developed especially for the EZ Series. Consumption of reagents is reduced by low volume analysis, yet high sensitivity is assured by a long optical path length. The limit of detection is in the low $\mu\text{g/L}$ range.

Results you can rely on

Smart automatic features for calibration, validation, priming and cleaning are embedded in the controller software and contribute to analytical performance, maximised uptime and negligible operator intervention. Precision micropumps dose all reagents. Sample lines and analysis vessel are cleaned with demineralised water to eliminate cross contamination between samples. Electronic and wet-chemical part of the analyser are strictly separated. A transparent door allows for instant visual inspection of the wet part.

Flexibility that meets your needs

EZ Series Sulphate Analysers come in an attractive, ergonomic mainframe with a compact footprint. All hardware is controlled by the integrated industrial panel PC. The modular build allows for the analyser to match your application and operational needs.

- The standard measuring range can be narrowed by a different calibration range or extended via internal dilution options.
- Analogue and digital output options
- Multiple stream analysis for up to 8 sample streams

There are many additional options available. Please contact Hach for more details.

Technické údaje

Alarm:	1x malfunctioning, 4x user-configurable, max. 24 VDC/0.5 A, potential free contacts
Analógové výstupy:	Active 4 - 20 mA max. 500 Ohm load, standard 1, max. 8 (option)
Automatické čistenie:	Áno
Č. prúdov vzoriek:	1, 2, 4, or 8
Certifikácia:	CE compliant / ETL certified
Demineralised water:	For rinsing / dilution
Detekčný limit:	$\leq 10 \text{ mg/L}$
Digitálne výstupy:	Optional: Modbus (TCP/IP, RS485)

Doba cyklu :	10 min (dilution + 5 min)
Earth connection:	Dry and clean earth pole with low impedance (< 1 Ohm) using an earth cable of > 2.5 mm ²
Hmotnosť:	25 kg
Instrument air:	Dry and oil free according to ISA-S7.0.01-1996 quality standard for instrument air
Interferencie:	Other metals that form complexes with EDTA, Silica > 500 mg/L, organic matter in water. Suspended or colloidal organic matter also may interfere with the endpoint. Large amounts of colour and turbidity interfere. Fats, oil, proteins, surfactants and tar.
Kalibrácia:	Automatic, 2-point; frequency freely programmable
Kvalita vzorky:	Maximum particle size 100 µm, < 0.1 g/L; Turbidity < 50 NTU
Materiál:	Hinged part: Thermoform ABS, door: PMMA
	Wall section: Galvanised steel, powder coated
Metóda merania:	Coloric measurement of turbidity at 450 nm after barium precipitation, conform with standard methods EPA 375.4 and APHA 4500-SO ₄
Model:	EZ1036
Napájanie:	100 - 240 VAC, 50/60 Hz
	Max. power consumption: 120 VA
Obsah balenia:	EZ1036 Sulphate Analyser, Instruction Manual, 1 x Double Bit Door Key, 1 x Mounting Brackets, 2 x Assembly Container 5L (for Buffer & BaCl ₂ Solution) and 1 x Assembly Container 2.5L (for EDTA Solution)
Odtok:	Atmospheric pressure, vented, min. Ø 32 mm
Parameter:	Sulphate
Presnosť:	Better than 3% full scale range for standard test solutions
Reagent Requirements:	Keep between 10 - 30 °C
Rozmery (V x Š x H):	690 mm x 465 mm x 330 mm
Rozsah merania:	10 - 40 mg/L SO ₄
	Optional:
	40 - 160 mg/L SO ₄ (with internal dilution)
	80 - 320 mg/L SO ₄ (with internal dilution)
	1000 - 4000 mg/L SO ₄ (with internal dilution)
Rýchlosť prietoku vzorky:	100 - 300 mL/min
Teplota prostredia:	10 - 30 °C ± 4 °C deviation at 5 - 95% relative humidity (non-condensing)
Teplota vzorky:	10 - 30 °C
Trieda ochrany:	Protection class: Analyser cabinet: IP44 / Panel PC: IP65
Validation:	Automatic; frequency freely programmable
Vzorka: tlak:	By external overflow vessel
Záruka:	24 mesiacov
Zdroj napájania:	100 - 240 VAC, 50/60 Hz

Obsah balenia

EZ1036 Sulphate Analyser, Instruction Manual, 1 x Double Bit Door Key, 1 x Mounting Brackets, 2 x Assembly Container 5L (for Buffer & BaCl₂ Solution) and 1 x Assembly Container 2.5L (for EDTA Solution)