



SC sensor cable, 100 m

Kat. číslo produktu:

LZY339

EUR Cena bez DPH:

Kontaktujte nás

Dátum odoslania neuvedené

Technické údaje

Dĺžka kábla:	100 m
Kódovanie drôtu:	AWG 22: brown (+12 V DC) black (circuit common) AWG 26: white (data -) blue (data +)
Materiál:	Cable: Cu: AWG 22 - 19×0.15 mm AWG 26 - 18×0.10 mm
Minimal bend radius:	7.5 × outer diameter, flexible installation
Minimal bend radius 2:	5 × outer diameter, fixed installation
Normálne napätie:	250 V Vpp
Odpor drôtu:	max. 106 Ω/km AWG 22 at 20 °C (loop)
Odpor izolácie:	≥ 20 MΩ × km at 20 °C
Odporová vlna:	ca. 95 Ω at 1 kHz, AWG 22 pairs
Odtienenie:	Cu- netting, tinned
Outside coat:	PUR (Elastoplan 1185), RoHS-conformal
Prevádzková teplota:	- 80 °C Fixed Installation
Priemer, vonkajší:	6.8 mm ± 0.3 mm
Shield attenuation:	≥ 55 dB
Skúšobné napätie:	1200 V Vrms

