




Be Right™



## SC sensor cable, 400 m

Kat. číslo produktu: LZY359

**ZASTARANÁ POLOŽKA**  
Táto položka už nie je dostupná.

---

### Technické údaje

Dĺžka kábla:	400 m
Kódovanie drôtu:	AWG 22: brown (+12 V DC) black (circuit common) AWG 26: white (data -) blue (data +)
Materiál:	Cable: Cu: AWG 22 - 19×0.15 mm AWG 26 - 18×0.10 mm
Minimal bend radius:	7.5 × outer diameter, flexible installation
Minimal bend radius 2:	5 × outer diameter, fixed installation
Normálne napätie:	250 V V <sub>pp</sub>
Odpor drôtu:	Max. 106 Ω/km AWG 22 at 20 °C (loop)
Odpor izolácie:	≥ 20 MΩ × km at 20 °C
Odporová vlna:	Approx. 95 Ω at 1 kHz, AWG 22 pairs
Odtienenie:	Cu- netting, tinned
Outside coat:	PUR (Elastoplan 1185), RoHS-conformal
Prevádzková teplota:	- 80 °C Fixed Installation
Priemer, vonkajší:	6.8 mm ± 0.3 mm
Shield attenuation:	≥ 55 dB
Skúšobné napätie:	1200 V V <sub>rms</sub>

wire/wire