



EZ9110 Heavy-duty Filtration System, pore size 50 µm

Kat. číslo produktu: EZ9110.XX310031

EUR Cena bez DPH: Kontaktujte nás

Dostupné

Universal self-cleaning filtration for difficult samples - compatible with all EZ Series online analysers

About the EZ9100 Series

The successful implementation of online analysers in process control strategies could not have been achieved without the development of a new generation of automatic sampling and sample preconditioning systems. The EZ9100 Series are the result of many years of field experience in combining analysers with filtration units.

Simplified operation by self-cleaning action

All preconditioning systems are designed for fully automatic operation and require virtually no human intervention. A blowback action by instrument air is incorporated in all systems. This fundamental design principle does not merely allow trouble-free sampling, moreover it contributes to high uptimes.

The EZ9110 is a filtration system developed to make solid-free samples from heavily charged liquids available for online analysis. Devoid of overly complex engineering, they can handle the difficult properties of wastewaters charged with high levels of insoluble constituents:

- Self-cleaning sample filtration with various pore sizes
- Large-bore pneumatic ball valves for sample and drain
- Automatic cleaning by solenoid controlled instrument air
- Static Pressure Regulator assures a constant, readily available sample level at atmospheric pressure
- PLC or analyser controlled cleaning frequency

Technické údaje

Č. prúdov vzoriek: 1 stream

Optional:

1 to 8 streams

Cleaning: Automatic blowback by solenoid controlled instrument air

Earth connection: Dry and clean earth pole with low impedance (< 1 Ohm) using an earth cable of > 2.5 mm²

Hmotnosť:	18 kg
Instrument air:	Dry and oil free according to ISA-S7.0.01-1996 quality standard for instrument air
Materiál:	Filter: SS 316L
	Piping: PVC
	Manual ball valves:PVC
	Tubing: Norprene, PFA, PE
	Panel: weather resistant Trespa
Napájanie:	24 VDC, powered by analyser
Odtok:	Overflow sample D=50 mm; overflow Static Pressure Regulator 3/8" OD
Required fast loop:	2 m/s
Rozmery (V x Š x H):	1150 mm x 750 mm x 200 mm
Size:	50 µm
Špeciálna poznámka:	Backflush valve controlled by Analyzer
Špeciálne funkcie:	Heavy Duty (Std)
Teplota vzorky:	Max. 65 °C
Trieda ochrany:	IP55
Veľkosť póru:	50 µm
	Optional:
	100 µm, 200 µm