



Kolorimetrický analyzátor chloru CL17sc s instalační sadou regulátoru tlaku, bez činidel

Kat. číslo produktu:	8574500
EUR Cena bez DPH:	Kontaktujte nás
Dodávka do 2 týždňov	

The Next Standard in Chlorine Analysis

The CL17sc online chlorine analyser extends Hach's decades-long legacy as the leader in online chlorine analysis. It uses EPA-approved colorimetric DPD analysis to deliver accurate and reliable measurements of free or total residual chlorine. Whether you use online chlorine measurements to optimise your process or report to regulatory agencies, the CL17sc is the analyser you can trust.

Connection to Hach's SC controller platform gives you more flexibility to transfer, store, and interact with your chlorine measurement data, resulting in better understanding and control of your process, more cost-effective decision-making, and greater peace of mind that your data is always there no matter what happens.

A built-in flow meter, three-colour status light, LED measurement cycle lights, and colorimeter window allow you to quickly and efficiently see that your CL17sc is functioning properly.

The CL17sc can also be used with Hach's Claros Water Intelligence System. With the innovative Claros Mobile Sensor Management, you can view measurements and instrument status anytime, anywhere, on any web-enabled device. Alerts for upcoming maintenance and issues requiring immediate attention are all in the palm of your hand. Detailed, step-by-step illustrated instructions for routine maintenance tasks also allow you to feel confident that you have performed routine maintenance correctly.

- Accurate, reliable online measurement of free or total residual chlorine
- Compliant with US EPA 40 CFR 141.74
- On-screen, guided workflows for routine maintenance tasks
- Comprehensive diagnostic features, including built-in flow meter, multi-colour status light, and colorimeter window
- Available Claros Mobile Sensor Management for measurement data and instrument status anytime, anywhere

Maintenance made easy

The CL17sc reduces your routine maintenance touch time with programmable alerts, simplified tubing replacement, and step-by-step maintenance instructions.

Peace of mind through comprehensive diagnostics

With upgraded features like a flow meter, colorimeter window, multi-colour status light, and predictive diagnostic software, you know your instrument is operating as intended.

Expanded connectivity. Increased flexibility.

By pairing the CL17sc with Hach's SC controller platform, your options increase significantly: internal data logging; external analogue and digital communication alternatives; and multi-parameter instrument flexibility.

The CL17sc is compliant with US EPA regulation 40 CFR 141.74. Both Method 4500-CL G and Method 334.0 can be used for measuring residual chlorine in drinking water.

Technické údaje

Alerts:	Nízka a vysoká koncentrace chloru. Znečištěná kyveta. Nízký a vysoký průtok vzorku.
Certifikácia:	CE compliant with: EN 61326-1, CISPR 11, EN 50581
	ACMA RCM
	South Korea KC Certificate
	North America: FCC Supplier’s Declaration of Conformance, IEC/EN 60529, ICES-003
Čistenie vzduchom:	Optional with 3/8-inch quick-connect fitting and tubing; 0.003 m ³ /min at 1.38 bar maximum
Detekčný limit:	0.03 mg/L
Doba cyklu :	2.5 minutes
Hmotnosť:	4.1 kg
Installation Kit:	Instalační sada regulátoru tlaku
Interferencie:	Other oxidising agents such as bromide, chlorine dioxide, permanganate, and ozone will cause a positive interference. Hardness must not exceed 1,000 mg/L CaCO ₃ .
Kompatibilita kontroléra:	SC200, SC1000, SC4500. All controllers sold separately
Krytie:	IP66
Obsah balenia:	Analyzátor chloru CL17sc s instalační sadou pro regulátor tlaku a evropskou uživatelskou příručkou.
	Kontrolér Hach SC a činidla nejsou součástí balení, prodávají se samostatně.
Odtok:	½-inch ID flexible hose
Parameter:	Chlorine, free; Chlorine, total residual
Požiadavky na napájanie (V):	12 V DC, maximálně 400 mA (napájeno prostřednictvím kontroléru)
Požiadavky na vzorku:	Y-strainer filtration with 40-mesh screen or higher
Presnosť:	± 5% or ± 0.04 mg/L (whichever is greater) from 0 - 5 mg/L Cl ₂
	± 10% from 5 - 10 mg/L Cl ₂
Prevádzková teplota:	5 - 40 °C
Prevádzková vlhkosť:	0 - 90% relative humidity, non-condensing
Prítok:	¼-inch OD polyethylene tube, quick-disconnect fitting
Rozmery (V x Š x H):	342 mm x 329 mm x 177 mm
Rozsah merania:	0 - 10 mg/L Cl ₂
Rýchlosť prietoku vzorky:	60 - 200 mL/min through the instrument
Spôsob inštalácie:	Wall mount
Spotreba reagentu:	0.5 L of buffer solution and 0.5 L of indicator solution in 31 days
Teplota vzorky:	5 - 40 °C
Tlak na prítoku:	0.3 - 5.2 bar supplied to Y-strainer
	0.1 - 0.3 bar supplied to analyser
Záruka:	24 mesiacov
Zdroj svetla:	LED, measurement at 510 nm, 1 cm light pathlength

Obsah balenia

Analyzátor chlóru CL17sc s instalační sadou pro regulátor tlaku a evropskou uživatelskou příručkou.Kontrolér Hach SC a činidla nejsou součástí balení, prodávají se samostatně.

Potrebné príslušenstvo

- SC4500 kontrolér, Prognosys, 5 x mA výstup, 2 digitálne sondy, 100 - 240 V AC, bez napájacieho kábla (Item LXV525.99A11551)
- SC4500 kontrolér, umožňujúci Claros, 5 x mA výstup, 2 digitálne sondy, 100 - 240 V AC, bez napájacieho kábla (Item LXV525.99AA1551)
- SC4500 kontrolér, umožňujúci Claros, 5 x mA výstup, 2 digitálne sondy, 100 - 240 V AC, zástrčka EÚ (Item LXV525.99CA1551)
- SC4500 kontrolér, Prognosys, 5x mA výstup, 1 digitálny sonda, 100 - 240 V AC, bez napájacieho kábla (Item LXV525.99A11501)
- SC4500 kontrolér, Prognosys, 5x mA výstup, 2 digitálne sondy, 24 V DC, bez zástrčky (Item LXV525.99Z11551)