




H₂S Calibration Gas Regulator, GS1440/GS2440EX

Kat. číslo produktu:	LXZ449.99.00023
EUR Cena bez DPH:	Kontaktujte nás
Dostupné	

This gas regulator contains non-gas equipment required for on-site calibration of the GS1440/GS2440EX sensor (measurement range 0 - 1000 ppm or 0 - 5 mg/L), including a flow regulator and a calibration cap.

Technické údaje

Obsah balenia:	Includes non-gas equipment required for on-site calibration of the GS1440/GS2440EX sensor.
	Please note that the 1000 ppm H ₂ S calibration gas (LCX449) required for the sensor calibration must be purchased separately.

Obsah balenia

Includes non-gas equipment required for on-site calibration of the GS1440/GS2440EX sensor. Please note that the 1000 ppm H₂S calibration gas (LCX449) required for the sensor calibration must be purchased separately.

Potrebné príslušenstvo

- H₂S Calibration Gas, 1000 ppm, GS1440/GS2440EX (Item LCX449)